




NOTES:

1. SUBSTRATE
BOROFLOAT®
2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
T(AVG) <1.0% @ 400 - 480nm
T(AVG) >80% @ 525 - 555nm
T(AVG) <1.0% @ 590 - 720nm
T(ABS) <1.0% @ 425 - 455nm
T(ABS) >70% @ 530 - 550nm
T(ABS) <1.0% @ 620 - 690nm

3. CUT AND SEAM

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	≥85 %	≥85 %
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

TITLE

50 x 50 GREEN DICHOIC FILTER

DWG NO

46139

SHEET
1 OF 1