


NOTES:

- 1. SUBSTRATE MATERIAL:  
N-BK7
- 2. ROHS COMPLIANT
- 3. SURFACE S1 IS PARALLEL TO SURFACE S2 WITHIN  $\leq 3$  ARCMIN
- 4. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 70% R  $\pm 5\%$  @ 550nm  
30% T  $\pm 5\%$  @ 550nm



S2: AR R(avg)  $\leq 1\%$ , R(abs)  $\leq 2\%$  @ 400 - 700nm

5. CUT WITH 0.25mm MAXIMUM EDGE CHIP



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO		TITLE	25 x 38mm, 70 R/30 T, PLATE BEAMSPLITTER	
ANGLE OF INCIDENCE	45°	45°		DWG NO	48400	SHEET 1 OF 1
SURFACE QUALITY	60-40	60-40				
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm				