



NOTES:

1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: Protected Gold (700-10000nm)  
R(AVG) >96% @ 700 - 2000nm  
R(AVG) >96% @ 2000 - 10,000nm
- S2: NONE

3. EDGES SEAMED

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	N/A
SURFACE FLATNESS	4 - 6λ	N/A
CLEAR APERTURE	24.13 x 24.13	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS IN mm

**Edmund Optics®**

TITLE	25.4 x 25.4mm Protected Gold, 4-6λ Mirror		
DWG NO	83496	SHEET 1 OF 1	