



NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING SPECIFICATION:
S1: Enhanced Aluminum (250-700nm)
R(AVG) >89% @ 250 - 450nm
R(AVG) >85% @ 250 - 700nm

3. FINE GROUND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	60-40	COMMERCIAL POLISH				
CLEAR APERTURE	25.50 x 25.50	N/A				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				

THIRD ANGLE PROJECTION	TITLE	30 x 30mm UV Enhanced Aluminum, λ/4 Mirror	
ALL DIMS IN mm	DWG NO	63171	SHEET 1 OF 1