



NOTES:

1. SUBSTRATE: FLOAT GLASS
2. LINE PAIR PATTERN: 100lp/mm
3. PARALLELISM:
 LINE TO LINE: ≤ 2 ARCSEC
 PATTERN TO SUBSTRATE: $\pm 1^\circ$
4. COATING:
 S1: VACUUM DEPOSITED CHROME, OD > 3.0
 REFLECTION: 50% \pm 5% @ 550nm

 S2: NONE
5. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
SURFACE QUALITY	60-40
SURFACE FLATNESS	1λ
BEVEL	PROTECTIVE AS NEEDED



ALL DIMS IN

in



TITLE	0.5" x 0.5" (100 lp/mm), Ronchi Ruling	
DWG NO	66341	SHEET 1 OF 1