






FOCAL LENGTH (EFL): $-150 \pm 1,5$
 BACK FOCAL LENGTH (BFL): $-152,63$

1 BLACKENED SURFACE


SURFACE A			SURFACE B		SURFACE C	
Øe 24			Øe 24		Øe 24	
			CEMENT: NOA 61 OR EQUIVALENT			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					25mm Dia x -150mm FL VIS 0, Inked, Negative Achromatic Lens	
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	624951NK
			SHEET SIZE			SHEET
			A4			1 OF 3




- 1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 92,3±0,092 CV Øe 24 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BK7 517/642	R 68,87±0,069 CV Øe 24 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE	25mm Dia x -150mm FL VIS 0, Inked, Negative Achromatic Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					DWG NO	624951NK		SHEET SIZE A4	SHEET 2 OF 3
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm					



LEFT SURFACE			MATERIAL		RIGHT SURFACE	
R 68,87±0,069 CX Øe 24 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -			GLASS N-SF5 673/322		R 204,15±0,204 CV Øe 24 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110			FIRST ANGLE PROJECTION 		 Edmund Optics® 25mm Dia x -150mm FL VIS 0, Inked, Negative Achromatic Lens	
			ALL DIMS IN: mm		TITLE 25mm Dia x -150mm FL VIS 0, Inked, Negative Achromatic Lens	
			DWG NO		62495INK	
					SHEET SIZE A4	
					SHEET 3 OF 3	