





NOTES:

1. SUBSTRATE: UV FUSED SILICA
2. ROHS: COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

	VALUE
SHAPE	PLANO
SURFACE QUALITY	80-50
CENTER WAVELENGTH (nm)	228
FULL WIDTH HALF MAX (FWHM) (nm)	25±5
MIN TRANSMISSION (%)	20
CLEAR APERTURE	Ø45.00
BEVEL	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics®**



THIRD ANGLE  
PROJECTION

TITLE

228nm, 25nm FWHM, 50mm DIA. FIRST  
SURFACE UV BANDPASS FILTER

ALL DIMS IN

mm

DWG NO

14916

SHEET  
1 OF 1