
NOTES:


1. SUBSTRATE: FUSED SILICA (CORNING 7980)


- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤0.4% @ 425 - 675nm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHEET 1 OF 1

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE (mm)	Ø36.00	Ø36.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

			Eamuna Optic	;S [®]
HIRD ANGLE . ROJECTION	\$	TITLE	40mm Dia., 4mm Thick, VIS 0° Coatec Fused Silica Window	, λ/4
ALL DIMS IN	mm	DWG NO	18330	SHEET