






**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
COLOR	Infrared
OUTPUT POWER (mW)	50
POWER STABILITY (%)	<2% RMS over 4 hours
WAVELENGTH (nm)	1064
MODULATION FREQUENCY (kHz)	1
FIBER LENGTH (m)	1.0



EO[®] Edmund Optics[®]

TITLE

Laser LC Turnkey 1064nm x 50mW Fiber SMA

DWG NO

19487

SHEET
1 OF 1