

1/4-20 Bumper (Package of 4), Sorbothane Bumpers



Stock #55-244 **6 In Stock**

⊖ 1 ⊕ C\$67⁵⁵

ADD TO CART

Volume Pricing

Qty 1-2	C\$67.55 each
Qty 3+	C\$59.92 each
Need More?	Request Quote

Product Downloads

General

English **Type:**
1/4-20 **Note:**

Physical & Mechanical Properties

25.40 **Thickness (mm):**

Sorbothane	Construction:
38.10	Diameter (mm):
30-65 / bumper	Load Capacity (lbs):
Threading & Mounting	
12.7	Thread Length (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.