

0 - 0.5", Quick Mini Digital Thickness Gage

See More by [Mitutoyo](#)



Stock **#78-359** NEW **1 In Stock**

-

1

+

C\$294⁵²

ADD TO CART

Volume Pricing	
Qty 1+	C\$294.52 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
	Range:
0 - 0.50 inches	
	Model Number:
700-118-30	

	Accuracy (inches):
±0.001	

Physical & Mechanical Properties	
0.0005	Resolution (inches):

Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- 0 – 0.5" Range with 0.0005" Resolution
- Easy-To-Read Digital LCD Display
- ABSOLUTE® Linear Scale Eliminates Need for Zeroing

Mitutoyo Thickness Gauges are designed to quickly measure the thickness of different materials or objects with high accuracy of $\pm 0.001"$. An ABSOLUTE® linear scale eliminates the need for setting the origin point everytime the gauge is powered on and prevents over speed errors. These thickness gauges feature ceramic spindles and anvils for high corrosion resistance and waterproof data output connectors to protect against dust, water, and oil ingress. Mitutoyo Thickness Gauges are ideal for quick inspection of a wide range of materials and objects including paper, film, wire, sheet metal, leather, and plastic parts. The grip handle, easy-to-reach lifting lever, spring-loaded spindle, and LCD display allow for quick, easy, and accurate measurements.