

[See all 12 Products in Family](#)

## (0-13mm Range), 0.01mm Increment, Metric Micrometer Head

See More by [Mitutoyo](#)



Stock #78-313 **1 In Stock**

- 1 + C\$122.<sup>50</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$122.50 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

0 - 13mm **Range:**  
148-801-10 **Model Number:**

### Physical & Mechanical Properties

±2 **Accuracy (µm):**

### Regulatory Compliance

## Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mike Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.

---

;