

TECHSPEC® 0.1 OD 12.5mm Diameter, Reflective ND Filter



Stock **#64-125** ☐ In Stock

-

1

+

C\$47.60

ADD TO CART

Qty 1-5
C\$47.60
Qty 6+
C\$37.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Angle of Incidence (°):
0

Optical Density OD (Average):
0.1

Substrate: Float Glass
Coating: Surface 1: Inconel
Reflection (%) : 10.00
Surface Quality: 80-50
Thickness (mm): 1.60 Nominal
Transmission (%) : 79.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%) : 80
Neutrality: ±3% of Transmission
Note: Optical density values are average over specified blocking wavelength range.
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant