

**TECHSPEC® 0.2 OD 25mm Diameter, Reflective ND Filter**



Stock **#64-133** ☐ In Stock

-

1

+

**C\$70.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| C\$70.00                      |
| Qty 6+                        |
| C\$56.00                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
25.00

Angle of Incidence (°):  
0

Optical Density OD (Average):  
0.2

|                                                                                                          |
|----------------------------------------------------------------------------------------------------------|
| <div>Substrate: <div></div></div> <div>Float Glass</div>                                                 |
| <div>Coating:</div> <div>Surface 1: Inconel</div>                                                        |
| <div>Reflection (%):</div> <div>14.00</div>                                                              |
| <div>Surface Quality:</div> <div>80-50</div>                                                             |
| <div>Thickness (mm):</div> <div>1.60 Nominal</div>                                                       |
| <div>Transmission (%):</div> <div>63.00</div>                                                            |
| <div>Type:</div> <div>Neutral Density Filter</div>                                                       |
| <div>Blocking Wavelength Range (nm):</div> <div>400 - 700</div>                                          |
| <div>Dimensional Tolerance (mm):</div> <div>±0.5</div>                                                   |
| <div>Clear Aperture (%):</div> <div>80</div>                                                             |
| <div>Neutrality:</div> <div>±3% of Transmission</div>                                                    |
| <div>Note:</div> <div>Optical density values are average over specified blocking wavelength range.</div> |
| <div>Surface Flatness (P-V):</div> <div>4 - 6λ</div>                                                     |

## Regulatory Compliance

|                                                        |
|--------------------------------------------------------|
| <div>RoHS 2015:</div> <div>Compliant</div>             |
| <div>Certificate of Conformance:</div> <div>View</div> |
| <div>Reach 235:</div> <div>Compliant</div>             |