

0.25° Axicon Angle, 480 - 580nm, Off-Axis Reflective Axicon

See More by [Cailabs](#)



Cailabs Canunda-Axicons

Stock **#14-556** CLEARANCE ☐ In Stock

-

1

+

C\$1,003.73

ADD TO CART

Qty 1+

C\$1,003.73

Volume Pricing

[Request Quote](#)

Get Product Downloads



Design Wavelength DWL (nm):
515

Diameter (mm):
25.40 +0.0/-0.1

Edge Thickness ET (mm):
8.0 +0.0/-0.15

Substrate: ☐
Aluminum

Surface Quality: 40-20
Type: Axicon, Off-Axis Reflective
Clear Aperture (%) : >90
Axicon Angle α (°) : 0.25 $\pm$ 1.5%
Coating Specification: R _{abs} >99% @480 - 580nm
Wavelength Range (nm) : 480 - 580
Coating Type: Dielectric
Damage Threshold, By Design: ☐ 0.2 J/cm ² @ 515nm, 500fs
Wavefront Error, P-V: < λ /10
Surface Roughness (nm) : <4 RMS
Off-Axis Angle (°) : 30

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View