

TECHSPEC[®] 0.25mm Thick, S-Mount Brass Spacer Ring



Brass Spacer Ring

Stock #63-959 20+ In Stock

-

1

+

C\$15⁷⁵

ADD TO CART

Volume Pricing	
Qty 1-4	C\$15.75 each
Qty 5-9	C\$14.70 each
Qty 10-25	C\$14.00 each
Need More?	Request Quote

Product Downloads

General

Spacer Ring

Function:

Physical & Mechanical Properties

0.25

Thickness (mm):

15.0

Outer Diameter (mm):

12.0	Inner Diameter (mm):
Threading & Mounting	
S-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Fit Over Male C, S, and T-Mount Threads
- Wide Range of Thicknesses Available for Accurate Spacing
- Spacer Ring Kits Available

TECHSPEC® C, S, and T-Mount Brass Spacer Rings fit over the male threads on our C, S, and T-Mount components, extending the overall length of the system. These spacer rings are ideal for making incremental adjustments to component spacing within an optical system. TECHSPEC® C, S, and T-Mount Brass Spacer Rings are available in thicknesses ranging from 0.25mm to 2.0mm, ensuring that application specific spacing is available. Kits of [C-Mount](#) and [S-Mount](#) Spacer Rings with 2 of each size can be found under the “Accessories” tab for this product. These spacer rings can be combined in multiple configurations to achieve the desired spacing distance.