


[See all 11 Products in Family](#)

Hamamatsu S12053-02 | 0.2mm UV-VIS (200-1000nm), Si APD

See More by [Hamamatsu](#)



Hamamatsu S12053, S9075, S5344, S5345 Series Si APD

Stock **#59-182** [CONTACT US](#)

-

1

+

C\$166^{.60}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$166.60 each
Qty 5-9	C\$154.00 each
Qty 10-24	C\$147.00 each
Need More?	Request Quote

Product Downloads

General	
0.39	Response Time (ns) R _L =50Ω:
S12053-02	Model Number:
TO-18	Package:
	Manufacturer:

Hamamatsu	
Physical & Mechanical Properties	
0.20	Active Area Diameter (mm):
Optical Properties	
200 - 1000	Spectral Response (nm):
0.14	Temperature Coefficient of BDV (V/°C):
620.00	Peak Sensitivity Wavelength (nm):
Electrical	
3.00	Terminal Capacitance (pF):
150/200 (Typical/Maximum)	Breakdown Voltage BDV, I _d =100μA (V):
900.00	Cut-Off Frequency (MHz):
0.20/5.00 (Typical/Maximum)	Dark Current I _d (nA):
0.42	Photosensitivity S (AW) @ λ _p :
80.00	Quantum Efficiency QE (%) @ λ _p :
50.00	Gain (M):
Environmental & Durability Factors	
-20 to 60	Operating Temperature (°C):
-55 to 100	Storage Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 197:
View	Certificate of Conformance:

Product Details

- High Sensitivity and Low Noise
- High-Speed Response
- Low-Light Level Measurement

Hamamatsu Avalanche Photodiodes (APDs) are silicon photodiodes with an internal gain mechanism. As with a conventional photodiode, absorption of incident photons creates electron-hole pairs. A high reverse bias voltage creates a strong internal electric field, which accelerates the electrons through the silicon crystal lattice and produces secondary electrons by impact ionization. The resulting electron avalanche can produce gain factors up to several hundred.

Si APDs are used when light signals are too high for photomultiplier tubes and too low for conventional photodiodes. Si APDs are often used in high-speed applications since the excess noise from the avalanche process is still lower than the noise that would be generated in connecting an external amplifier to a conventional photodiode operated at high frequencies. Typical applications include low-light level measurement, spectroscopy, range finding and spatial/fiber optic communication. Both our short-wavelength type and near infrared detection types are hermetically sealed in a metal package with a clear glass window.

Photosensitivity (S) and Quantum Efficiency (QE): For the NIR and UV/MS Si APDs, λ=800nm and λ=620nm, respectively. QE and S are given for M equal to 1.

Gain (M) is given at λ=800nm and λ=650nm for the NIR and UV/MS Si APDs respectively.

Terminal capacitance is measured at the gain specified.