

TECHSPEC®

0.3 OD 25mm Diameter, Reflective ND Filter



Stock **#30-933** ☐ In Stock

-

1

+

C\$70.00

ADD TO CART

Qty 1-5
C\$70.00
Qty 6+
C\$56.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
0

Optical Density OD (Average):
0.3

Substrate:  Float Glass
Coating: Surface 1: Inconel
Reflection (%) : 21.00
Surface Quality : 80-50
Thickness (mm) : 1.60 Nominal
Transmission (%) : 50.00
Type : Neutral Density Filter
Blocking Wavelength Range (nm) : 400 - 700
Dimensional Tolerance (mm) : ±0.5
Clear Aperture (%) : 80
Neutrality : ±5% of Optical Density
Note : Optical density values are average over specified blocking wavelength range.
Surface Flatness (P-V) : 4 - 6λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant