


0.5 OD 12.5mm Dia, Absorptive ND Filter

See More by [Hoya](#)



Stock **#48-526** ☐ In Stock

1

C\$43.40

ADD TO CART

Qty 1-10
C\$43.40
Qty 11+
C\$39.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Optical Density OD (Average):
0.5 ±0.05

Glass/Filter Number: Hoya ND-25
Substrate: ☐ ND Filter Glass
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 535
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.5
Transmission (%): 32.0 (average)
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.1
Parallelism (mm): <0.02

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant