


0.5" Travel, Eng Micrometer, Solid-Top Ball Bearing Stage



2.62" Center drive stage and its X-Y configuration

Stock **#38-994** ☐ In Stock

1

C\$796.60

ADD TO CART

Qty 1+

C\$796.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement: Linear (X)
Guide System: Ball Bearing
Type of Drive: English Micrometer
Drive Orientation: Side Drive
Type: English
Stage Size (mm): 66.5 x 66.5
Travel (inches): 0.5
Construction: Aluminium Stage
Graduation (inches): 0.001
Height (inches): 1.00
Height (mm): 25.4
Load Capacity, Normal (lbs): 62
Note: Solid Top
Stage Size (inches): 2.62 x 2.62
Straight Line Accuracy (inches): 0.00008/inch of travel
Weight (lbs): 0.92
Thrust Capacity, T_a (lbs): 10
Thrust Capacity, T_b (lbs): 2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View