

0.5" Travel, X Axis, Micro Series (B)



Stock #38-531 ☒ In Stock

-

1

+

C\$366.80

ADD TO CART

Qty 1+

C\$366.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Fine Screw (80 Pitch)

Drive Orientation:
Center Drive

Type: English
Stage Size (mm): 16.8 x 44.2
Travel (mm): 12.7
Travel (inches): 0.5
Center Hole: 0.275" (7.0mm) Thru with 5/16-24 TPI Thread
Construction: Aluminum Body, Stainless Steel Rails
Load Capacity, Normal (kg): 0.34
Note: Without Covered Rails
Stage Size (inches): 0.66 x 1.74
Straight Line Accuracy (µm): 1
Weight (g): 16
Wobble (mrad): 0.01

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View