

0.5" Travel, XYZ Axes, Micro Series with Covered Rails (B)



Stock **#56-424** ☐ In Stock

1

C\$1,041.60

ADD TO CART

Qty 1+
C\$1,041.60
Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Linear (X-Y-Z)

Guide System:
Ball Bearing

Type of Drive:
Fine Screw (80 Pitch)

Drive Orientation:
Center Drive

Type: English
Stage Size (mm): 19.1 x 44.2
Travel (mm): 12.7
Travel (inches): 0.5
Center Hole: 0.275" (7.0mm) Thru with 5/16-24 TPI Thread
Construction: Aluminum Body, Stainless Steel Rails
Load Capacity, Normal (kg): 0.34
Note: With Covered Rails
Stage Size (inches): 0.75 x 1.74
Straight Line Accuracy (µm): 1.5
Weight (g): 60
Wobble (mrad): 0.01

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View