

TECHSPEC® 0.6 OD 25mm Diameter UV-VIS ND Filter



Stock #49-065 ☐ In Stock

-

1

+

C\$161.00

ADD TO CART

Qty 1-5

C\$161.00

Qty 6+

C\$128.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.20

Optical Density OD (Average):
0.6

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:

Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.10
Transmission (%): 25.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 250 - 700
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant