

0.6 OD M39.0 x 0.50, Mounted Absorptive ND Filter



Stock **#59-171** ☐ In Stock

-

1

+

C\$60.20

ADD TO CART

Qty 1-9
C\$60.20
Qty 10+
C\$56.84
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.6

Clear Aperture CA (mm):
34.0

Filter Thread:
M39 x0.50

Substrate: ☐
ND Filter Glass

Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Transmission (%): 25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 41.0 ±0.3
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View
