

0.6 OD M46.0 x 0.75, Mounted Absorptive ND Filter



Stock **#54-734** CLEARANCE ☐ In Stock

-

1

+

C\$48.93

ADD TO CART

Qty 1+
C\$48.93

Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average): 0.6
Clear Aperture CA (mm): 42.0
Filter Thread: M46 x0.75
Substrate: ☐ ND Filter Glass
Thickness with Mount (mm): 5.00

Surface Quality: 80-50
Transmission (%): 25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 4.4 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 48.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.4

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View