

0.65" x 5.95", 0.38" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#46-108** **5 In Stock**

⊖ 1 ⊕ C\$74²⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | C\$74.20 each |
| Qty 11-49 | C\$67.20 each |
| Need More? | Request Quote |

Product Downloads

General

Fresnel Lens **Type:**

Physical & Mechanical Properties

0.06 **Center Thickness CT (inches):**

±0.05 **Dimensional Tolerance (inches):**

Dimensions (inches):

0.65 x 5.95

Dimensions (mm):

16.51 x 151.13

Effective Size (inches):

0.38 x 5.95

Thickness Tolerance (inches):

±0.020

Optical Properties

Effective Focal Length EFL (mm):

9.65

Substrate:

Acrylic

Coating:

Uncoated

Wavelength Range (nm):

400 - 1100

Effective Focal Length EFL (inches):

0.38

Groove Density (grooves/inch):

200.00

Index of Refraction (n_d):

1.49

Transmission (%):

85 (Typical)

Environmental & Durability Factors

Operating Temperature (°C):

80 (Maximum)

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 242:

[Compliant](#)

Product Details

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

Technical Information

