

[All Products](#) / [Imaging Lenses](#) / [Zoom Lenses](#) / [Dynamic Focus VZM™ Lens](#)

[See all 5 Products in Family](#)

0.65X - 4.6X Dynamic Focus VZM™ Lens



Dynamic Focus VZM™ Lens

Stock **#89-999** CLEARANCE ☐ In Stock

- 1 +

C\$2,039.73

ADD TO CART

Qty 1+

C\$2,039.73

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
248.00

Filter Thread:
M22.5 x0.50

Working Distance Tolerance (mm):
±3

Zoom Ratio:
7:1

Type:
Zoom Lens

Primary Magnification PMAG: 0.65X - 4.6X
Maximum Sensor Format: 2/3"
Working Distance (mm): 87.00
Style: Liquid Lens
Lens Wavelength Range: VS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
