

0.75" Travel, Fine Screw, Thru-Hole Ball Bearing Stage



45mm/1.75" Center drive stages and optional brackets

Stock **#36-484** [CONTACT US](#)



1



C\$676.20

ADD TO CART

Qty 1+

C\$676.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Fine Screw (64 Pitch)

Drive Orientation:
Center Drive

Type:
English

Stage Size (mm): 44.4 x 44.4
Travel (inches): 0.75
Construction: Aluminium Stage
Graduation (inches): No
Height (inches): 0.75
Height (mm): 19.1
Load Capacity, Normal (lbs): 25
Note: Thru-Hole
Stage Size (inches): 1.75 x 1.75
Straight Line Accuracy (inches): 0.00008/inch of travel
Weight (lbs): 0.5
Thrust Capacity, T_a (lbs): 10
Thrust Capacity, T_b (lbs): 5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View