

0.75X Mag, InfiniGage CW Precision Spacer

See More by [Infinity Photo-Optical Company](#)



Stock **#64-872** **1 In Stock**

-

1

+

C\$109²⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$109.20 each
Need More?	Request Quote

Product Downloads

General

Type:	
Lens Accessory	
Compatible Lens:	
#64-877	

Optical Properties

Horizontal Field of View, 1/2" Sensor:	
8.5mm	
Horizontal Field of View, 1/3" Sensor:	
6.4mm	

39.00	Working Distance (mm):
0.75X	Magnification:

Threading & Mounting

C-Mount	Mount:
---------	--------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Accurate Measurements Based on Field of View
 - 7 Spacer Options for a Wide Range of Magnifications
 - UV Option Available
- The InfiniGage™ main lens mates with seven precision spacers for multiple magnification and working distance choices. Simply set InfiniGage™ to the desired magnification and begin making accurate measurements. The Infinigage™ accepts 11.8mm to 12.5mm diameter filters for polarization or color analysis without changing outer dimensions. The InfiniGage™ can be doubled in magnification by simply adding a DL Doubler Tube, reducing the FOV by a factor of two. The Infinigage™ is also available in UV which is optimized for best performance from 250nm-700nm.
- Note:** InfiniGage™ CW option is only compatible with CWPrecision Spacers.

Technical Information

	Magnification	Working Distance	Field of View on 1/2" Sensor	Field of View on 1/3" Sensor
InfiniGage Precision Spacer with 2X Amplifier (Optional)	0.25X	286mm	25.6mm	19.2mm
	0.5X	155mm	12.8mm	9.6mm
	0.66X	120mm	9.7mm	7.3mm
	1.0X	85mm	6.4mm	4.8mm
	1.3X	72mm	4.9mm	3.6mm
	1.5X	67mm	4.3mm	3.2mm
	2.0X	52mm	3.2mm	2.4mm