

0.9 OD M40.5 x 0.50, Machine Vision Absorptive ND Filter



Stock **#21-667** ☐ In Stock

- 1 +

C\$94.50

ADD TO CART

Qty 1-9
C\$94.50
Qty 10+
C\$90.72
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.9

Clear Aperture CA (mm):
35.50

Filter Thread:
M40.5 x 0.50

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 12.50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
