

0.9 OD M77 x 0.75, Machine Vision Absorptive ND Filter



Stock **#21-412** ☐ In Stock

-

1

+

C\$236.60

ADD TO CART

Qty 1-9
C\$236.60
Qty 10+
C\$224.84
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.9

Clear Aperture CA (mm):
73.00

Filter Thread:
M77 x0.75

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 12.50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
