

1-18, 101.6 x 101.6mm NBS 1963A Negative Target



NBS 1963A Resolution Target

Stock **#85-275** ☐ In Stock

-

1

+

C\$271.60

ADD TO CART

Qty 1-4

C\$271.60

Qty 5+

C\$259.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:
Vacuum deposited durable chromium pattern

Frequency (lp/mm):
1-18

Substrate:
Float Glass

Optical Density OD (Average):

≥3.0
Pattern Size (mm): 42.9 x 40.9
Dimensions (mm): 101.6 x 101.6
Surface Quality: 60-40
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.100
Type: Negative
Dimensional Tolerance (mm): ±0.100
Note: Pattern Location is Centered
NIST Certification: No
Changes in Frequency Steps: 1.1, 1.25, 1.4, 1.6, 1.8, 2.0, 2.2, 2.5, 2.8, 3.2, 3.6, 4.0, 4.5, 5.0, 5.6, 6.3, 7.1, 8.0, 9.0, 10.0, 11.0, 12.5, 14.0, 16.0, 18.0
Line Width Tolerance (µm): ±2.7 - 1.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
