

1-18, 50.8 x 50.8mm NBS 1963A Resolution Target Negative



NBS 1963A Resolution Target

Stock **#39-856** ☐ In Stock



1



C\$357.00

ADD TO CART

Qty 1-4

C\$357.00

Qty 5+

C\$340.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:

Vacuum deposited durable chromium pattern

Frequency (lp/mm):

1-18

Substrate:

Float Glass

Optical Density OD (Average):

≥3.0
Pattern Size (mm): 45.5 x 44.5
Dimensions (mm): 50.8 x 50.8 ±0.51
Surface Quality: 20-10
Thickness (mm): 1.50
Type: Negative
NIST Certification: No
Changes in Frequency Steps: 1.1, 1.25, 1.4, 1.6, 1.8, 2.0, 2.2, 2.5, 2.8, 3.2, 3.6, 4.0, 4.5, 5.0, 5.6, 6.3, 7.1, 8.0, 9.0, 10.0, 11.0, 12.5, 14.0, 16.0, 18.0
Line Width Tolerance (µm): ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View