

1-2" Diameter, Optical Mount



Stock #53-964 ☐ In Stock

-

1

+

C\$326.20

ADD TO CART

Qty 1-9

C\$326.20

Qty 10+

C\$311.50

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Clear Aperture CA (inches):
0.81 ([#36-461](#)) / 1.81 ([#36-465](#))

Clear Aperture CA (mm): 20.6 (#36-461) / 46.0 (#36-465)
Optical Centerline (mm): 50.8
Range: 10°
Dimensions (inches): 3.75 x 2.00 x 3.50
Dimensions (mm): 95.3 x 50.8 x 88.9
Weight (lbs): 1.3
Inner Diameter (inches): 2.25 x 20 TPI
Construction: Black Anodized Aluminum, Stainless Steel
Diameter of Compatible Optics (inches): 1.0 or 2.0
Optical Centerline (inches): 2.00
Optic Holding Style: #36-461 Required (for 1"/25mm) #36-465 Required (for 2"/50mm)
Max. Thickness of Compatible Optics (mm): 22.0 (#36-461) / 22.0 (#36-465)
Adjustment Screw Pitch (inches): 0.015

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View