

[All Products](#) / [Test Targets](#) / [Resolution Test Targets](#) / [Star Target](#)

[See all 4 Products in Family](#)

Siemens Star Target, 4" x 4", 60 Sectors Chrome on Glass



Siemens Star Target, 4" x 4", 60 Sectors Chrome on Glass

Stock **#46-247** ☐ In Stock



1



C\$436.80

ADD TO CART

Qty 1-4

C\$436.80

Qty 5+

C\$415.38

Volume Pricing

[Request Quote](#)

Get Product Downloads

Frequency (lp/mm):
0.31 - 7.14

Substrate:
Float Glass

Line Width (mm):
1.6 - 0.070

Number of Sectors:

60.00
Optical Density OD (Average): >2.8
Pattern Diameter (mm): 62.5
Dimensions (inches): 4 x 4 ±0.004
Thickness (mm): 1.50 ±0.100
Wedge Angle: 6°
Unresolved Core Diameter (mm): 2.7
Note: Sputtered Chrome Coated
NIST Certification: No

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
