

## 1" Travel, 0.001" Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#33-733** **2 In Stock**

⊖ 1 ⊕ C\$142<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	C\$142.80 each
Qty 10-24	C\$128.52 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Type:  
English

Manufacturer:  
Mtutoyo

### Physical & Mechanical Properties

Travel (inches):  
1

Graduation (inches):

0.001	
10	<b>Stem Diameter (mm):</b>
Plain/Spherical	<b>Stem/Spindle:</b>
15	<b>Stem Length (mm):</b>
6.35	<b>Spindle Diameter (mm):</b>
27	<b>Min. Spindle Length (mm):</b>
18	<b>Max. Diameter (mm):</b>
95.5	<b>Overall Length (mm):</b>

## Hardware & Interface Connectivity

English Micrometer	<b>Type of Drive:</b>
--------------------	-----------------------

## Regulatory Compliance

<a href="#">Exempt</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>REACH 241:</b>

## Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
  - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential. Please reference individual product descriptions to see which stages are compatible with each drive mechanism.