

1" Travel, 2.62"L x 2.62"W Ball Bearing Slide



Linear Motion Ball Bearing Slides



Stock **#37-356** ☐ In Stock

-

1

+

C\$344.40

ADD TO CART

Qty 1+

C\$344.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Manual

Type:
English

Stage Size (mm): 66.5 x 66.5
Travel (inches): 1
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Height (inches): 1.00
Load Capacity, Normal (lbs): 40.0
Mounting Threads: (8) 10-32 on Top
S.H.C.S. C'bore: (2) #1/4 on Base
Stage Size (inches): 2.62 x 2.62
Straight Line Accuracy (inches): 0.00008/inch of travel
Weight (lbs): 0.6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View