

TECHSPEC® 10" Diameter x 100" FL Uncoated, Parabolic Mirror



Stock #35-726-000 ☐ In Stock

- 1 + **C\$2,900.80**

ADD TO CART

Qty 1-2
C\$2,900.80
Qty 3+
C\$2,465.40
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±1.5

Surface Quality: 60-40

Surface Accuracy: λ/8

Diameter (inches): 10.00 +0.06/-0
Diameter (mm): 254.00 +1.5/-0
Effective Focal Length EFL (inches): 100.0
Effective Focal Length EFL (mm): 2,540.00
Radius of Curvature (mm): 5,080.00
Aperture (f/#): f/10
Coating: Uncoated
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 229
Edge Thickness ET (inches): 1.75
Edge Thickness ET (mm): 44.50
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View