

TECHSPEC[®] 10" x 12", 1.1mm Thick, Uncoated, Gorilla Glass® Window



Gorilla® Glass Windows



Stock #21-238 ☐ In Stock

1

C\$150.50

ADD TO CART

Qty 1-5

C\$150.50

Qty 6+

C\$115.85

Volume Pricing

[Request Quote](#)

Get Product Downloads



Bevel:
Protective as needed

Chemical Strengthening Cycle (hours):
8

Clear Aperture (%) : 90.00
Clear Aperture CA (mm) : 228.6 x 274.3
Dimensions (mm) : 254 x 304.8 ±0.5
Thickness (mm) : 1.10 ±0.05
Coating : Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 7.58 (0 to +300°C)
Density (g/cm³) : 2.39
Edges : Cut and Seamed
Index of Refraction n_d : 1.5
Poisson's Ratio : 0.22
Substrate : Gorilla® Glass
Surface Quality : 80-50
Type : Protective Window
Wavelength Range (nm) : 350 - 2200
Young's Modulus (GPa) : 70
Length (inches) : 10.00
Width (inches) : 12.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 233 : Compliant