

100mm Diameter 0-1.5 OD, Circular ND Filter



Stock **#49-086** ☐ In Stock

1 **C\$442.40**

ADD TO CART

Qty 1-9
C\$442.40
Qty 10+
C\$398.30
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
100.00

Angle of Incidence (°):
0.00

Optical Density OD (Average):
0.04 - 1.5

Substrate: ☐
[B270](#)

Inner Diameter (mm): 8.3
Coating: Variable
Thickness (mm): 2.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Parallelism (arcmin): 3.00
Optical Density Tolerance (%): ±8
Coating Specification: Continuously Variable Inconel from 0 - 310°

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View