

100mm Diameter Unmounted 0.04-3.0 OD, Circular Variable Neutral Density (ND) Filter



Mounted Circular Variable Neutral Density (ND) Filters



Stock **#43-769** ☐ In Stock

1

C\$499.80

ADD TO CART

Qty 1-10
C\$499.80
Qty 11+
C\$449.82
Volume Pricing
Request Quote

Get Product Downloads

Angle of Incidence (°):
0.00

Optical Density OD (Average):
0.04 - 3.0

Substrate: ☐

B270
Inner Diameter (mm): 25.4
Coating: Variable
Outer Diameter (mm): 100.0
Surface Quality: 60-40
Thickness (mm): 1.52
Thickness Tolerance (mm): ±0.25
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Parallelism (arcmin): ±3
Dimensional Tolerance (mm): ±0.10 ID, ±0.20 OD
Optical Density Tolerance (%): ±5
Linearity (%): ±5
Coating Specification: Continuously Variable Inconel from 0 - 270°
Mount: Unmounted

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View