

75mm Max. Aperture, Burnished Steel Leaves Iris Diaphragm



Standard Series

Stock **#57-586** ☐ In Stock

-

1

+

C\$427.00

ADD TO CART

Qty 1-4

C\$427.00

Qty 5+

C\$376.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:

Unmounted

Minimum Aperture (mm):

4.0, Typical

Maximum Aperture (mm):

75.0

Outer Diameter (mm):

100.0
Construction: Anodized Aluminum Alloy, Burnished Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 15.00
Number of Leaves: 20.00
Thickness (mm): 9.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant