

1.00" x 11.9", 0.75" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#46-110** [CONTACT US](#)



1



C\$77.00

ADD TO CART

Qty 1-10

C\$77.00

Qty 11+

C\$67.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):

19.05

Substrate: ☐

Acrylic

Coating:

Uncoated

Type:

Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 1.0 x 11.9
Dimensions (mm): 25.4 x 302.26
Effective Focal Length EFL (inches): 0.75
Effective Size (inches): 0.75 x 11.9
Groove Density (grooves/inch): 200.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Transmission (%): 85 (Typical)
Thickness Tolerance (inches): ±0.020

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View