

100X Nikon CFI60 TU Plan Epi ELWD Infinity Corrected Obj

See More by [Nikon](#)



100X Nikon CFI60 TU Plan Epi ELWD, #58-519

Stock **#58-519** ☐ In Stock

-

1

+

C\$8,509.20

ADD TO CART

Qty 1+
C\$8,509.20

Volume Pricing
Request Quote

Get Product Downloads

Field of View (mm):

0.22

Horizontal Field of View, 1/2" Sensor:

0.06mm

Horizontal Field of View, 2/3" Sensor:

0.09mm

Focal Length FL (mm):

2.00

Model Number:

MJE21900
Length excluding Threads (mm): 55.40
Magnification: 100X
Maximum Diameter (mm): 30
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.80
Mounting Threads: M25 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 0.3
Depth of Field (µm): 0.43
Field of View, 25 Diameter Field Eyepiece (mm): 0.25
Field of View, 22 Diameter Field Eyepiece (mm): 0.22
Working Distance (mm): 4.5
Weight (g): 215.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 22
Parfocal Length (mm): 60
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View