

101.6mm Clear Aperture 33R/67T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock **#39-492** ☐ In Stock

-

1

+

C\$786.80

ADD TO CART

Qty 1-10

C\$786.80

Qty 11+

C\$668.78

Volume Pricing

[Request Quote](#)

Get Product Downloads



Clear Aperture CA (mm):
101.6

Coating:
Dielectric

Coating Specification:
33/67 @ 400 - 700nm

Construction: Pellicle
Diameter (mm): 114.30
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 6.35
Reflection/Transmission Ratio (R/T): 33/67 $\pm$ 5%
Substrate: ☐ Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Wavelength Range (nm): 400 - 700
Mounting Threads: 2-56
Thickness (μm): 2 +0.3/-0.0

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View