

TECHSPEC® 101.6mm Dia., Enhanced Aluminum, 4-6λ Mirror



Stock **#18-924** ☐ In Stock

1

C\$75.60

ADD TO CART

Qty 1-5

C\$75.60

Qty 6+

C\$59.50

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
101.60 +0.00/-0.25

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Coating Specification: R_{avg} ≥95% @ 450 - 650nm @ 45°
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 91.44
Edges: Ground, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00 (nominal)
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Damage Threshold, By Design: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant