

[See all 3 Products in Family](#)

## 10.5 x 14mm FL, Grade 1, Double-Convex Lens



Stock #76-749 CLEARANCE **14 In Stock**

1  C\$14<sup>.35</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$14.35 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Double-Convex Lens **Type:**

#### Physical & Mechanical Properties

10.50 **Diameter (mm):**

#### Optical Properties

14.00 **Effective Focal Length EFL (mm):**

**f#:**

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

1 - 14.9mm Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

