

105mm Dia x 145mm FL Cold Mirror Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock **#90-974** ☐ In Stock

-

1

+

C\$679.00

ADD TO CART

Qty 1-10
C\$679.00
Qty 11+
C\$597.10
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ BOROFLOAT®

Coating:
Cold Mirror, 0°

Coating Type:
Metal

Center Hole Diameter (mm):

27.0
Height (mm): 42.0
Inner Diameter (mm): 99
Outer Diameter (mm): 105.00 +0.0/-0.5
Type: Specialty Mirror
Distance to Focal Point f₁ (mm) : 22
Distance to Focal Point f₂ (mm): 145

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
