

[All Products](#) / [Laser Optics](#) / [Laser Optical Assemblies](#) / [Beam Shapers](#) / [AdlOptica πShaper Flat Top Beam Shapers](#)

[See all 24 Products in Family](#)

1064nm HP Flat Top Beam Shaper | πShaper 12_12_1064_HP_W

See More by [AdlOptica](#)



Stock **#21-101** [CONTACT US](#)

⊖ 1 ⊕ **C\$13,619.20**

ADD TO CART

Qty 1-4
C\$13,619.20
Qty 5+
C\$12,257.00
Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm): 1064
Diameter (mm): 49.00
Entrance Beam Diameter, 1/e² (mm): 12.0 – 12.1
Model Number:

πShaper 12_12_1064_HP_W
Length (mm): 360.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <580
Wavelength Range (nm): 1020 - 1100
Style: Flat Top
Damage Threshold, By Design: ☐ 3 J/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 12.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant