

10° Diffusing Angle 25mm Dia., Fused Silica Holographic Diffuser



Holographic UV Diffusers

Stock **#48-506** [CONTACT US](#)

- 1 +

C\$640.50

ADD TO CART

Qty 1+

C\$640.50

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (°):
±1

Diffusing Angle (°):
10 (FWHM)

Clear Aperture CA (mm):
21.6 ±0.1

Diameter (mm):
25.00 ±0.1

Operating Temperature (°C):
-40 to +170

Substrate: 
[Fused Silica](#) (Corning 7980)

Transmission (%):
Typical: 90

Type:
Holographic Diffuser

Wavelength Range (nm):
400 - 700

Construction:
Mounted

Mount Thickness (mm):
4.7 ±0.1

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)